Magnetic Hotplate Stirrers

Magnetic stirrer is developed for demanding applications. It is widely used in chemical synthesis, physical and chemical analysis, bio-pharmaceuticals, to name a few, etc. Combining with glass ceramic work plate, brushless DC motor, external temperature sensor and the work plate temperature optimized up to 550°C.

MS7-H550-Pro

LCD Digital Magnetic Hotplate Stirrer

Features

- LCD display for precise monitoring of speed and temperature
- Built-in PID controller ensures the safe heating of the medium with overheating protection
- Max. Heating plate temperature 550°C
- Glass ceramic work plate provides excellent chemical resistant performance and most efficient heat transfer
- External temperature control is possible by connecting the temperature sensor(PT 1000) with an accuracy at ±0.2°C
- Digital speed controlling, Max. speed at 1500rpm
- Outstanding brushless DC motor performance enables more stirring power
- Two rotating knobs enable the easy and direct change of speed and temperature
- The "HOT" warning will flash when the work plate temperature is above 50°C even if the hotplate is turned off
- Remote function provides PC control and data transmission





Wide range of accessory



Chemical resistance

Specifications

Work plate Dimension [W x D]
Work plate material
Motor type
Motor rating input
Motor rating output
Power
Heating output
Voltage
Stirring positions
Max. stirring quantity, [H₂O]
Max. magnetic bar[length]
Speed range
Speed display
Temperature display
Heating temperature range
Temperature control accuracy
Overheating protection
Temperature display accuracy
External temperature sensor
"Hot" warning
Data connector
Protection class
Dimension [W x D x H]
Weight
Permissible ambient temperature and humidity

184x184mm (7 inch)
Glass ceramic
Brushless DC motor
18W
10W
1050W
1000W
100~120/200~240V 50/60Hz
1
20L
80mm
100~1500rpm
resolution ±1rpm
LCD
LCD
Room Temp550°C, increment 1°C
±1°C(<100°C) ±1%(>100°C)
580°C
±0.1°C
PT1000 (accuracy ±0.2)
50°C
RS232
IP21
215x360x112mm
5.3kg
5~40°C 80%
5~40°C 80%

ติดต่อบริษัท นีโอนิคส์ จำกัด Tel: 02-077-7602 หรือ 061-8268939

E-mail: sale@neonics.co.th เว็บไซต์ www.neonics.biz