

_									
S	D	е	CI	ıtı	IC	а	tı	0	ns

HI97734 Free and Total Chlorine HR

	Range (all methods)	0.00 to 10.00 mg/L (as Cl _z)				
Chlorine	Resolution (all methods)	0.01 mg/L				
	Accuracy @25°C (77°F) (all methods)	±0.03 mg/L ±3% of reading at 25 °C				
	Method	Adaptation of EPA DPD method 330.5				
	Light Source	light emitting diode				
	Bandpass filter	525 nm				
Measurement	Bandpass filter bandwidth	8 nm				
System	Bandpass filter wavelength accuracy	±1.0 nm				
	Light Detector	silicon photocell				
	Cuvette type	round 24.6 mm diameter (22 mm inside)				
	Auto logging	50 readings				
	Display	128 x 64 pixel B/W LCD with backlight				
Additional	Auto-off	after 15 minutes of inactivity (30 minutes before a READ measurement)				
Specifications	Battery type / Life	alkaline 1.5 V AA (3) / > 800 measurements (without backlight)				
	Environment	0 to 50°C (32 to 122°F); 0 to 100% RH, non-serviceable				
	Dimensions	142.5 x 102.5 x 50.5 mm (5.6 x 4.0 x 2.0")				
	Weight	380 g (13.4 oz.)				

HI97734 is supplied with sample cuvettes (2), sample caps (2), plastic stoppers (2), 1.5V AA batteries (3), instrument quality certificate, and instruction manual. CAL Check standards and testing reagents sold separately

Ordering Information

HI97734C includes photometer, CAL Check standards, sample cuvettes (2), sample caps (2), plastic stoppers (2), 1.5V AA batteries (3), cuvette wiping cloth, scissors, CAL Check standard certificates, instrument quality certificate, instruction manual, and HI7101412 rigid carrying case.

Reagents sold separately

Reagents and Standards

HI97734

HI97734-11 CAL Check standard cuvettes for free and total chlorine HR

HI93734-01 free and total chlorine HR reagent for 100 tests HI93734-03 free and total chlorine HR reagent for 300 tests

ติดต่อบริษัท นีโอนิคส์ จำกัด

Tel: 02-077-7602 หรือ 061-8268939

E-mail: sale@neonics.co.th เว็บไซต์ www.neonics.biz

HI97734

Free and Total Chlorine HR Portable Photometer

Advanced LED optical system

- Innovative optical design that utilizes a reference detector and focusing lens to eliminate errors from changes in the light source and from imperfections in the glass cuvette.
- LEDs have a much higher luminous efficiency, providing more light while using less power. They also produce little heat, which could otherwise affect electronic stability.

CAL Check™

Validate instrument performance at any time using CAL Check cuvettes made with NIST traceable standards. The CAL Check screen guides the user step-by-step through the validation process and user calibration.

• On-screen tutorial mode with animations

- Guides users step-by-step through the measurement process
- Waterproof and floating IP67 case
- Unit of measure is displayed along with reading
- Built-in timer
- Built-in reaction timer that ensures consistency between tests.

• Error messages on display

- · Alerts to problems including no cap, high zero, and standard too low
- GLP data
 - · Displays the last calibration date.
- Auto logging
- · Battery status indicator
- Auto-shut off

Significance of Use

Chlorine is one of the most cost-effective disinfectants used in a variety of different applications. Its use varies from light application in surface sanitation, to heavy duty disinfection of medical devices, to removal of microorganism infections in piping systems. The advantage of using chlorine over peroxide-type disinfectants is that chlorine is not only a strong oxidant, it also is capable of breaking tough chemical bonds found in cell walls or biofilms. Correct and effective use of chlorine helps to destroy disease-causing pathogens, reduce odors, and eliminate bacteria.